



# dB Blocker® Convertible Solid

*The dB Blocker Convertible Solid offers the highest degree of protection.*

The dB Blocker Convertible Solid™ offers the same protection as the dB Blocker Solid™, but has the optional removable cord. It is custom fit to the individual wearer for maximum comfort using Skinsoft™ medical silicone. It is particularly suited for industrial applications where there are high air levels (wind noise).


## RECOMMENDED USES:

- Any industrial application
- Manufacturing plants
- Glass plants (hot end)
- Motorcycle riding
- Shooting / target practice
- Welding

*The use of this protector is not limited to the above applications.*

## FEATURES:

- Achieves an NRR of 28
- Custom molded to each employee
- Removable cord
- Cast retained for 5 years
- Colored exterior



## BENEFITS:

- Highest amount of actual work place hearing protection
- Less noise induced stress leading to less accidents and absenteeism
- A hearing protector that is comfortable to wear will enhance compliance with the hearing protection program
- The dB Blocker gives each worker the same amount of hearing protection
- A lost dB Blocker can be easily replaced
- The cord attachment can match your job specifications
- Product can be manufactured without a cord if it might cause a safety hazard
- Color option makes them easier to find if dropped and allows managers to see if employees are wearing them at a glance around plant floor
- The protectors can be made detectible by a metal detector

Custom Protect Ear Inc.

T: 604.599.1311 ● Toll: 1.800.520.0220 ● F: 604.599.7377 ● E: [hear@protectear.com](mailto:hear@protectear.com)



SPECIFICATIONS:

- Skinsoft™ medical grade silicone material
- Hypoallergenic
- Non-porous
- Durometer of 30 (800 PSI tear strength)
- 25 lbs tear strength on metal anchor
- Product inert to 500 F
- Metal detectible optional
- Cord options:
  - Cotton – strongest
  - Plastics – washable
  - Metal impregnated – metal detectible
- Colors available:
  - Blue
  - Green
  - Orange
  - Red
  - Black
  - Purple
  - Clear
  - Beige



CARE AND MAINTENANCE:

- Lubrication with Petroleum Jelly (supplied) is essential for first 2 weeks
- Wash regularly with soap and warm water
- Re-lubricate as needed after washing